




Overhanging Floorstand, open



Installation example




Connection version 1:
Square cap




Connection version 2:
Handwheel



Connection version 3:
Position indicator



Connection version 4:
Actuator




Rails for head plate



Angle frame




Support plate



Ground plate (pre-drilled)



Rod support




Wall installation incl. bolts

scan me!



Standard-Set-Selection



① Floorstand (Please tick/complete):

without rod, incl. bolts | Article No.: 19302

② Connection on top (Please tick/complete):

Square cap SQ27/32 with set screw | Article No.: 12109.07-VK-SS

Handwheel Ø400 mm DN250-350 SQ27/32 | Article No.: 13893.00

Screw set M12x20 mm incl. bolt and washer | Article No.: 10174

Mechanical position indicator, aluminium | Square insert 26 mm:

Turns/stroke 13 | Article No.: 13910.26

Turns/stroke 47 | Article No.: 13909.26

Turns/stroke 140 | Article No.: 13907.26

Turns/stroke 470 | Article No.: 13908.26

Turns/stroke 1390 | Article No.: 13918.26

Mechanical position indicator, stainless steel | Square insert 26 mm:

Turns/stroke 14 | Article No.: 13026.14RZW

Turns/stroke 47 | Article No.: 13026.47RZW

Turns/stroke 140 | Article No.: 13026.140RZW

Turns/stroke 470 | Article No.: 13026.470RZW

Electrical position indicator, stainless steel | Square insert 26 mm:

Turns/stroke 14 | Article No.: 13026.14EZW

Turns/stroke 47 | Article No.: 13026.47EZW

Turns/stroke 140 | Article No.: 13026.140EZW

Turns/stroke 470 | Article No.: 13026.470EZW

③ Head plate version (Please tick/complete):

Head plate suitable for rod | Article No.: 19333.V2A

Head plate F10 | Article No.: 1107027A

Head plate F14 | Article No.: 1107027B

④ Adjustable extension (Please tick/complete):

Standard lengths (L) | Square tube: upper: 25x25 mm | lower: 30x30 mm:

Material: 1.4301 (V2A)

Material: 1.4301 (V4A)

L0,50 - 0,75 m | Article No.: 17400.V2A

L0,50 - 0,75 m | Article No.: 17400.V4A

L0,70 - 1,15 m | Article No.: 17401.V2A

L0,70 - 1,15 m | Article No.: 17401.V4A

L1,00 - 1,75 m | Article No.: 17402.V2A

L1,00 - 1,75 m | Article No.: 17402.V4A

L1,20 - 2,20 m | Article No.: 17403.V2A

L1,20 - 2,20 m | Article No.: 17403.V4A

L1,50 - 2,60 m | Article No.: 17404.V2A

L1,50 - 2,60 m | Article No.: 17404.V4A

L1,90 - 3,50 m | Article No.: 17405.V2A

L1,90 - 3,50 m | Article No.: 17405.V4A

L2,20 - 4,00 m | Article No.: 22971.V2A

L2,20 - 4,00 m | Article No.: 22971.V4A

L2,60 - 5,00 m | Article No.: 22970.V2A

L2,60 - 5,00 m | Article No.: 22970.V4A

L3,20 - 5,50 m | Article No.: 17406.V2A

L3,20 - 5,50 m | Article No.: 17406.V4A

L3,60 - 6,50 m | Article No.: 22972

L4,30 - 7,70 m | Article No.: 20522

L4,30 - 7,70 m | Article No.: 11738

⑤ Wall brackets (Please tick):

Wall bracket for rod guidance on both sides, swivelling:

(incl. interchangeable insert)

Length: 45 - 400 mm | Article No.: 21303

Length: 45 - 600 mm | Article No.: 21304

Wall bracket for extensions, suitable for square 20, square 25, square 30:

(incl. interchangeable insert)

Length: 45 - 400 mm | Article No.: 11732

Length: 45 - 600 mm | Article No.: 11768

Length: 400 - 1000 mm | Article No.: 22912

⑥ Connection below (Please tick/complete):

Please select coupling on p.9 and fill in the article no.:

Article No.: _____

Remarks:

Subject to technical modifications!

send

